

995841 Mono/Adjala townline
RR#1 Rosemont
Ontario, Canada
L0N 1R0

Toll free | 866.888.8981
Tel | 705.435.3780
Fax | 705.435.3770

info@interspecsystems.com

> Recessed Patient Console

Patient Service Consoles provide the services required in general patient care, emergency, labour and delivery rooms and other areas where relatively few services are required.

The patient consoles allow rapid, low cost installation for both new construction and renovation.



These units are built to the needs of each hospital and location. They may contain electrical devices such as receptacles, switches, timer switches, dimmers, nurse call and code blue, digital elapsed timers, medical gas outlets and many more options. The flush mounted patient console is six inches wide and may be any length. The 2^{7/8} inch backbox depth allows back-to-back installation when consoles are used in adjacent rooms, yet will not allow sound transmission when insulated.



> Recessed Patient Console Specifications

Basic construction: Backbox shall be a 16 gauge formed satin coat steel with combination 1/2 inch and 3/4 inch knockouts on the top and bottom of the backbox. Electrical conduit runs to the knockouts, wiring within the console shall be the responsibility of the electrical contractor. Medical gas outlets and piping shall be installed in the consoles by the mechanical contractor. Individual fixed barriers; separating different voltages and mechanical services, shall be installed by Interspec Systems.

Components: Individual components of the patient service console shall be to the following specifications:

Power Outlets: Power receptacles shall be provided in the types and quantities shown on the drawings and shall be Hospital grade. The power receptacles shall be CSA/U.L. listed.

Grounding Jacks: Externally accessible grounding jacks shall be provided in the console at the locations shown on the shop drawings.

Medical Gas Station Outlets: Oxygen, Vacuum, Medical Air, Evacuation, Nitrous Oxide outlets shall be as indicated in plans and specifications.

Provisions for the following components or devices provided and installed by others shall meet the following requirements:

All nurse call equipment shall be furnished and installed by others as indicated in the plans and specifications.

P.S.C. Consoles meet the requirements of CSA & UL and comply with NFPA. 99. accordance with local electrical code requirements.



995841 Mono/Adjala townline
RR#1 Rosemont
Ontario, Canada
L0N 1R0

Toll free | 866.888.8981
Tel | 705.435.3780
Fax | 705.435.3770

info@interspecsystems.com